

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 600

Lewatit® MonoPlus MP 600 is a strongly basic, macroporous anion exchange resin (type II) with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer, designed for all demineralization applications. The monodisperse beads have high chemical and osmotic stability. The extremely high monodispersity (uniformity coefficient: max. 1.1) and very low fines content of max. 0.1 % (<0.350 mm) result in particularly low pressure losses compared with standard resins. Due to its special macroporous structure **Lewatit® MonoPlus MP 600** stands for effective adsorption and desorption of naturally occurring organic substances. Due to the excellent regeneration efficiency and high operating capacity **Lewatit® MonoPlus MP 600** is generally used for waters in which silica and carbon dioxide concentrations are moderate. For higher silica feeds, a type I anion exchange resin such as **Lewatit® MonoPlus MP 800** is recommended.

Lewatit® MonoPlus MP 600 is especially suitable for:

» demineralization of water for industrial steam generation operated with co-current or modern counter-current systems like e.g. Lewatit® WS System, Lewatit® Liftbed System or Lewatit® Rinsebed System
» polishing using the Lewatit® Multistep System or a conventional mixed bed arrangement in combination with **Lewatit® MonoPlus SP 112** or **Lewatit® MonoPlus SP 112 (H)**
» working mixed bed in combination with **Lewatit® MonoPlus SP 112 (H)**

Lewatit® MonoPlus MP 600 adds special features to the resin bed:

- » high flow rates during regeneration and loading
- » a good utilization of the total capacity
- » a low demand for rinse water
- » a homogeneous throughput of regenerants, water and solutions, resulting in a homogeneous operating zone
- » a virtually linear pressure drop gradient across the entire bed depth, allowing operation with higher bed depths
- » good separation of the components in mixed bed applications

During the application of type II anion exchange resins in the regenerated form the strongly basic groups are gradually converted to weakly basic ones. This process is an inherent property of the functional groups and enhanced by:

- » elevated oxygen concentrations (e.g. downstream from a degassifier)
- » the presence of iron, manganese, copper, etc.
- » regeneration temperatures >25°C
- » operating temperatures >30°C

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies (LPT).

This document contains important information
and must be read in its entirety.

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 600

General Description

Ionic form as shipped	Cl ⁻
Functional group	Quaternary amine, type II
Matrix	Crosslinked polystyrene
Structure	Macroporous
Appearance	Beige, opaque

Specified Data

	metric units	
Uniformity Coefficient	max.	1.1
Mean bead size	mm	0.6 (+/- 0.05)
Total capacity	min. eq/l	1.1

Physical and Chemical Properties

		metric units	
Bulk density	(+/- 5 %)	g/l	630
Density		approx. g/ml	1.10
Water retention		wt. %	55 - 60
Volume change	Cl ⁻ --> OH ⁻	max. vol. %	12
Stability	at pH-range		0 - 14
Storability	of the product	max. years	2
Storability	temperature range	°C	-20 - +40

This document contains important information and must be read in its entirety.

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 600

Recommended Operating Conditions*

		metric units	
OPERATION			
Operating temperature		max. °C	30
Operating pH-range			0 - 12
Bed depth		min. mm	800
Specific pressure drop	(15 °C)	approx. kPa*h/m ²	1.0
Pressure drop		max. kPa	300
Linear velocity	operation	max. m/h	50
REGENERATION, COUNTER-CURRENT			
Regenerant	type		NaOH
Regenerant	quantity	approx. g/l	40
Regenerant	concentration	approx. wt. %	2 - 4
Linear velocity		approx. m/h	5
Linear velocity	rinsing	approx. m/h	5
Rinse water requirement	slow / fast	approx. BV	3.5
REGENERATION, CO-CURRENT			
Regenerant	type		NaOH
Regenerant	quantity	approx. g/l	100
Regenerant	concentration	approx. wt. %	3 - 5
Linear velocity		approx. m/h	5
Linear velocity	backwash (20 °C)	approx. m/h	10
Linear velocity	rinsing	approx. m/h	5
Rinse water requirement	slow / fast	approx. BV	7
Bed expansion	backwash (20 °C)	approx. % per m/h	11.5
Freeboard	backwash (extern / intern)	vol. %	100

* The recommended operating conditions refer to the use of the product under normal operating conditions. It is based on tests in pilot plants and data obtained from industrial applications. However, additional data are needed to calculate the resin volumes required for ion exchange units. These data are to be found in our Technical Information Sheets.

This document contains important information and must be read in its entirety.

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 600

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

Lanxess Deutschland GmbH
BU LPT
D-51369 Leverkusen

www.lpt.lewatit.com
www.lanxess.com

This document contains important information
and must be read in its entirety.